


## appliance description

### ELEKTRONIK


Safety foot pedal FE-FS1-S2DO2V-U-xx



The foot pedal FE-FS1-S2DO2V-U have 3 positions with a pressure point and a pedal lock with manual release, to control dangerous movements (for instance get down of a press brake ect...). It has 2 working contacts (2NO) to drive the movement and one safety switches (2 positive opening NC contacts) to stop the movement. Pressing the foot pedal, till the pressure point, allows the changeover of the 2 working contacts. Once the pressure point is got over, the positive opening safety contact is activated in order to initiate immediately the dangerous movement.

Thus a redundant information for the safety circuit is available.

A restart of the machine is only possible after releasing the foot switch.





# appliance description

### Safety foot pedal FE-FS1-S2DO2V-U-xx

Execution	1-aluminum foot pedal heavy version, Pedal lock with manual release, free standing on slip elastic feet
Operating voltage	max. 500 VAC, 40-60Hz
Switching current	max. 10 A. For inductive and capacitive loads, a contact protection must be provided.
Operations	min. 10 Mio.
Contact Material	Silver
Connection type	Screwterminal
Electrical connection	0,5-1,5 mm2
Cable entry	M20x1,5
Switching insert	2 NO contacts, after pressure point 2 NC contacts, positive opening
Switching function	Sequential circuit with pressure point
pressure point	Min. 200 N operating force when use as intended
Switching system	Jump-/ creep mechanism
Housing	Die cast aluminum, powder-coated RAL 7021 (dark gray)
Pedal	Die cast aluminum, powder-coated RAL 7021 (dark gray)
Accident cover	Die cast aluminum, powder-coated
Attachment	For mounting of the footpedal in the housing bottom (pedal area) are provided $2x\emptyset4,5$ and $2x\emptyset6,5$ holes (see drawing). Here threads can be cut. Alternatively, the rubber feet can be removed and these threads can be used as a mounting option.
Protection type	IP65 to IEC/EN 60529
Operating temperature	-30°C to +80°C
Regulations	IEC/EN 60947-5-1
Order code	FE-FS1-S2DO2V-U-xx (xx = RD = cover firered RAL 3000)

#### Additional information:

Any modification of the foot pedal and its components will void the warranty and product liability.

In particular, lifting the die-cast aluminum pedal against the upper stop and driving out the retaining pin are prohibited.

This can cause the foot pedal to malfunction and thus lead to a loss of safety!

Telefon: 0711 / 91 96 97-0 Internet: http://www.fiessler.de Telefax: 0711 / 91 96 97-50 eMail: info@fiessler.de